

MICROFLEX® 93-868 LIFESTAR EC PRODUCT SET UP

PRODUCT NAME

Preferred Product Name:

MICROFLEX® 93-868 LifeStar EC

Acceptable Alternate:

MICROFLEX® 93-868

DESCRIPTION

Short Description (50 words)

MICROFLEX® 93-868 LifeStar EC provides two layers of reliable barrier protection against hazardous substances and high-risk patient handling. A dual layer, dual color design and low 0.65 AQL provides advanced barrier protection for more demanding tasks. Designed with non-stick and non-foaming properties for reduced interference and increased productivity.

Long Description (75 words)

MICROFLEX® 93-868 LifeStar EC provides two layers of reliable barrier protection against hazardous substances and high-risk patient handling.

- Features a dual layer, dual color design for two layers of protection
- · Tested for protection from a variety of hazardous chemicals
- Delivers advanced barrier protection with a low 0.65 AQL
- Designed with non-stick and non-foaming properties for reduced interference and increased productivity

PACKAGING

100 gloves per dispenser, 10 dispensers per shipper carton, 1,000 gloves per shipper carton

UPC Barcodes

	S (6½-7)	M (7½-8)	L (8½-9)
EAN/GTIN Inner	10076490436367	10076490436374	10076490436381
EAN/GTIN Outer	20076490436364	20076490436371	20076490436388
	XL (9½-10)	XXL (10½-11)	XXXL (11½-12)
EAN/GTIN Inner	10076490436398	10076490436404	10076490436411
EAN/GTIN Outer	20076490436395	20076490436401	20076490436418

Product Images







Download MICROFLEX® 93-868 product images <u>HERE</u>



MICROFLEX® 93-868 LIFESTAR EC PRODUCT SET UP

Weight (kg)

	S (6½-7)	M (7½-8)	L (8½-9)
Inner Case Gross Weight	0.94	1.02	1.13
Outer Case Net Weight	8.50	9.50	10.70
Outer Case Gross Weight	9.83	10.68	11.78
	XL (9½-10)	XXL (10½-11)	XXXL (11½-12)
Inner Case Gross Weight	XL (9½-10) 1.20	1.35	1.29
Inner Case Gross Weight Outer Case Net Weight			

Dimensions (length x width x height)

Inner carton			
S (6.5-7.0) - XXL (10.5-11)	270 x 130 x 80		
Outer Case	420 x 275 x 290		

APPLICATION IMAGES







Download application images **HERE**.

VIDEOS



Download product video <u>HERE</u>. View on YouTube <u>HERE</u>.

ADDITIONAL SUPPORT MATERIALS

Performance Standards













